

Nominal Rating, kV	Minimum Phase-to Phase Center Line Spacing Inches (mm)				Distance to Nearest Grounded Object in Path of Fuse Exhaust (from center line of hinge insulator)
	SMD-50 Power Fuse ^①	Vertical-Break Disconnecting Switches ^② (IEEE Std. C37.30.1)	Horn-Gap Switches (IEEE Std. C37.46)	Expulsion (fiber tube) Fuses (IEEE Std. C37.46)	
	Vertical, Vertical Offset, or Right- Angle Mounting				
34.5	27 (686)	36 (914)	60 (1524)	60 (1524)	53 (1346)
46	30 (762)	48 (1219)	72 (1829)	72 (1829)	60 (1524)
69	41 (1041)	60 (1524)	84 (2134)	84 (2134)	79 (2007)

① Hinge is assumed connected to load side of circuit, not to source side.

② Without arcing horns



Supersedes Data Bulletin 212-81 dated February 13, 1989

August 28, 2017

© S&C Electric Company 1964-2017, all rights reserved

Information Bulletin 212-81