


Station Style Mountings (Vertical-offset style illustrated)



Style	Rating, kV			Spacing—Parallel-Connected Mountings, Inches (mm)		
	Nom.	Max	BIL	F		D <sup>③</sup>
				Min <sup>①</sup>	Max <sup>②</sup>	
Station—Vertical-offset	14.4	17.0	110	12 (305)	18 (457)	—
Station—Right-angle	25	27	150	15 (381)	21 (533)	—
Station—Inverted	34.5	38	200	20 (508)	26 (660)	—

① Minimum spacing must be maintained to avoid having live parts in such close proximity as to distort significantly the dielectric field in the vicinity of the interrupting elements of the fuse.

② Maximum spacing limitations should be observed. In addition, source- and load-side conductors feeding each pair of parallel fuses

should be arranged symmetrically to avoid bus configurations having unequal lengths (and therefore, unequal impedances).

③ See S&C Information Bulletin 242-81 for appropriate phase spacing.



Supersedes Data Bulletin 242-82 dated 8-5-85.

October 28, 2019

© S&C Electric Company 1985-2019, all rights reserved